

# NMLT38

## Straight Non-Metallic Connectors



Straight Non-Metallic Connector

Country of Origin: USA

Weight: 0.039 lbs/each

Height: 1.410"

Width: 1.410"

Material(s): UV-Rated Plastic

Conduit Type: Non-Metallic Liquid Tight Conduit, Type B Only

Knockout Size(s): 1/2"

Trade Size: 3/8"

### Packaging

Unit: 25 pcs

Standard: 100 pcs



**Arlington**<sup>®</sup>

1 Stauffer Industrial Park  
Scranton, PA 18517  
800/233.4717  
Fax 570/562.0646  
[www.aifittings.com](http://www.aifittings.com)

# NMLT38

## Straight Non-Metallic Connectors



Straight Non-Metallic Connector

Country of Origin: USA

Weight: 0.039 lbs/each

Height: 1.410"

Width: 1.410"

Material(s): UV-Rated Plastic

Conduit Type: Non-Metallic Liquid Tight Conduit, Type B Only

Knockout Size(s): 1/2"

Trade Size: 3/8"

### Packaging

Unit: 25 pcs

Standard: 100 pcs



**Arlington®**

1 Stauffer Industrial Park  
Scranton, PA 18517  
800/233.4717  
Fax 570/562.0646  
[www.aifittings.com](http://www.aifittings.com)