

NMLT9038

90 Degree Non-Metallic Connectors



90 Degree Non-Metallic Connector

Country of Origin: USA

Weight: 0.053 lbs/each

Height: 2.305"

Width: 2.460"

Material(s): UV-Rated Plastic

Conduit Type: Non-Metallic Liquid Tight Conduit, Type B Only

Knockout Size(s): 1/2"

Trade Size: 3/8"

Packaging

Unit: 10 pcs

Standard: 50 pcs



Arlington®

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

NMLT9038

90 Degree Non-Metallic Connectors



90 Degree Non-Metallic Connector

Country of Origin: USA

Weight: 0.053 lbs/each

Height: 2.305"

Width: 2.460"

Material(s): UV-Rated Plastic

Conduit Type: Non-Metallic Liquid Tight Conduit, Type B Only

Knockout Size(s): 1/2"

Trade Size: 3/8"

Packaging

Unit: 10 pcs

Standard: 50 pcs



Arlington[®]

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com