

A Arlington

Part : NMLT9038

Description: 90° Non-Metallic Connector

Listing: ULCSA

Country of Origin: USA

Weight: 0.053 lbs/each

Height: 2.440"

Width: 2.325"

Additional Color Options:  height="16" width="16"/>

Material(s): UV Rated Plastic

Conduit Type: Non-Metallic Liquid Tight Conduit, Type B Only

Knockout Size(s): 1/2"

Trade Size: 3/8"

Packaging

Unit: 10 pcs

Standard: 50 pcs



A Arlington

Part : NMLT9038

Description: 90° Non-Metallic Connector

Listing: ULCSA

Country of Origin: USA

Weight: 0.053 lbs/each

Height: 2.440"

Width: 2.325"

Additional Color Options:  <http://www.aifittings.com/catalog/images/colors/black.png> height="16" width="16"

Material(s): UV Rated Plastic

Conduit Type: Non-Metallic Liquid Tight Conduit, Type B Only

Knockout Size(s): 1/2"

Trade Size: 3/8"

Packaging

Unit: 10 pcs

Standard: 50 pcs

