

# NMLT9050

## 90 Degree Non-Metallic Connectors



90 Degree Non-Metallic Connector

Country of Origin: USA

Weight: 0.058 lbs/each

Height: 2.242"

Width: 2.460"

Material(s): UV-Rated Plastic

Conduit Type: Non-Metallic Liquid Tight Conduit, Type B Only

Knockout Size(s): 1/2"

Trade Size: 1/2"

### Packaging

Unit: 10 pcs

Standard: 50 pcs



**Arlington®**

1 Stauffer Industrial Park  
Scranton, PA 18517  
800/233.4717  
Fax 570/562.0646  
[www.aifittings.com](http://www.aifittings.com)

# NMLT9050

## 90 Degree Non-Metallic Connectors



90 Degree Non-Metallic Connector

Country of Origin: USA

Weight: 0.058 lbs/each

Height: 2.242"

Width: 2.460"

Material(s): UV-Rated Plastic

Conduit Type: Non-Metallic Liquid Tight Conduit, Type B Only

Knockout Size(s): 1/2"

Trade Size: 1/2"

### Packaging

Unit: 10 pcs

Standard: 50 pcs



**Arlington®**

1 Stauffer Industrial Park  
Scranton, PA 18517  
800/233.4717  
Fax 570/562.0646  
[www.aifittings.com](http://www.aifittings.com)