



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## NTL885TRLACC6 Radiant Nlite/2 15A TR Outlts + Louv La

*Pass & Seymour/Legrand*

|                  |   |
|------------------|---|
| Catalog Number   | NTL885TRLACC6   |
| Manufacturer     | Pass & Seymour/Legrand  |
| Description      | Perfect For Adding A Little Light Just Where You Need It, Without Sacrificing An Outlet or Dealing With Unattractive Plug-In Models, This Built-In Night Light From The Radiant Registered Collection Comes Combined With A Tamper-Resistant Outlet. A Great Upgrade For Hallways and Kids' Bedrooms, It Installs Easily In Place Of A Standard Outlet and Automatically Comes On In The Dark. With Five Adjustable Light Levels, You Can Easily Set Its Brightness to Meet Your Preferences or Needs. Features The Sleek, Clea |
| Weight per unit  | 0.2800 (lbs/each)   |
| Product Category | Gen Purpose Recept & Surge Pro  |

### Features

|                       |                  |
|-----------------------|------------------|
| amperage rating       | 15               |
| Contact Configuration | 15A              |
| Contact Rating        | 125              |
| indoor/outdoor        | Indoor           |
| Mounting Type         | Box              |
| operating cycles      | 50000.0          |
| Outlet Type           | Tamper-Resistant |
| Voltage Rating        | 125              |

### Material, Color, and Finish

|        |       |
|--------|-------|
| Finish | Matte |
|--------|-------|

### Dimensions and Weight

|      |  |
|------|--|
| Size | Depth 1.5" x Width 1.6" x Height 2.75" |
|------|--|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | RADIANT NLITE/2 15A TR OUTLTS + LOUV LA   |
| extra long description | P&S NTL885TRLACC6 RADIANT NLITE/2 1   |
| Features               | Nightlight  |
| Long Description       | Perfect for adding a little light just where you need it, without sacrificing an outlet or dealing with unattractive plug-in models, this built-in night light from the radiant Registered Collection comes combined with a tamper-resistant outlet. A great upgrade for hallways and kids' bedrooms, it installs easily in place of a standard outlet and automatically comes on in the dark. With five adjustable light levels, you can easily set its brightness to meet your preferences or needs. Features the sleek, clea |
| Product Type           | Radiant Nlite/2 15A TR Outlts + Louv La   |
| Special Features       | Night Light   |

## Manufacturer Information

|                           |                        |
|---------------------------|------------------------|
| Brand                     | LEGRAND-PASS & SEYMOUR |
| GTIN                      | 00785007032376         |
| Manufacturers Part Number | NTL-885TRLACC6         |
| UPC                       | 785007032376           |

## Taxonomies, Classifications, and Categories

|                      |                                      |
|----------------------|--------------------------------------|
| Category Description | Residential Switches                 |
| Type                 | Outlet, Nightlight, Tamper-Resistant |

## Trade Size

|          |      |
|----------|------|
| Amperage | 15.0 |
|----------|------|

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 6    |
| Weight Per each | 0.28 |

## Uses, Certifications, and Standards

|                          |  |
|--------------------------|--|
| Application              | Residential                              |
| environmental conditions | Flammability Rating: UL 94 V2            |
| Mounting                 | BOX                                      |
| nema rating              | 15A                                      |
| Operating Temperature    | Maximum continuous +115°C, minimum -40°C |
| standard                 | UL, CULUS, cULus, UL Listed              |