

P1100 SERIES

SWIMMING POOL TIMERS, 24 HOUR ELECTROMECHANICAL CONTROL



QUICK INSTALL/RELEASE LEVER: For easy installation and removal when installing into pool panels.

LOAD INDICATOR LAMP

CONVENIENT EXTERNAL ROCKER SWITCH: 3 position switch: OFF/ON/AUTO. Use switch to turn OFF pump at the end of pool season.

REAL TIME SWITCH FACE: Easy to set and check time.

CAPTIVE TRIPPERS: 15 minute intervals, no lost trippers.

HEATER CONTACTS: FM suffix includes "Fireman Switch" to turn off pool heater 20-30 minutes before timer turns OFF. Contact rates SPST, 15A @120V.

THERMOSTAT: PFP models include built in Freeze Protection. No extra wiring. Thermostat turns on load at user settable level between 33°F and 42°F. Moving water prevents costly freeze damage.

ACCESSORY CONTACT: PF models include extra contact to accept PFPT Freeze Protection Accessory. Thermostat turns ON load at user settable level between 33°F and 42°F. Moving water prevents costly freeze damage.

TIMER INTERLOCK: Makes one second timer dependant on operation of another timer.

ORDERING INFO

| CATALOG NO. | UPC CODE | INPUT SUPPLY (VAC) 60Hz | CONTACTS | RESISTIVE/INDUCTIVE RATINGS | HP RATING | NOTES |
|-------------|----------|-------------------------|----------|-----------------------------|-----------------------------|--|
| PFP2-M | 94026 | 240 | DPST | 40A | 7.5HP @ 240V | Thermostat only |
| PFP3-M | 94027 | 120/240 w/neutral | DPST | 40A | 3 HP @ 120V 7.5HP @ 240V | Thermostat only |
| P1101-M | 10056 | 120 | DPST | 40A | 3 HP @ 120V | |
| P1101FM-M | 10060 | 120 | DPST | 40A | 3 HP @ 120V | Fireman Switch |
| PF1101-M | 94020 | 120 | DPST | 40A | 3 HP @ 120V | Accepts PFPT thermostat input |
| PF1101FM-M | 94024 | 120 | DPST | 40A | 3 HP @ 120V | Fireman Switch & Accepts PFPT thermostat input |
| PFP1102-M | 94022 | 240 | DPST | 40A | 7.5HP @ 240V | Freeze Protection included |
| PFP1103-M | 94023 | 120/240 w/neutral | DPST | 40A | 3 HP @ 120V 7.5HP @ 240V | Freeze Protection included |
| P1104-M | 10057 | 240 | DPST | 40A | 7.5HP @ 240V | |
| P1104FM-M | 10061 | 240 | DPST | 40A | 7.5HP @ 240V | Fireman Switch |
| PF1104-M | 94021 | 240 | DPST | 40A | 7.5HP @ 240V | Accepts PFPT thermostat input |
| PF1104FM-M | 94025 | 240 | DPST | 40A | 7.5HP @ 240V | Fireman Switch & Accepts PFPT thermostat input |
| P1101-2M | 10058 | 120 | DPST | 40A | 2HP @ 120V | Replacement for PP-20R-2P1 |
| P1104-2M | 10059 | 240 | DPST | 40A | 5HP @ 240V | Replacement for PP-20R-2P4 |

NOTE: "❄️" = Indicates Freeze Protection.