



*Quick Thread™ device hole



Nail-On

Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
			D	W	H			
18.0	P-181	Single gang, angled mid-nails	2-5/8	2-5/16	3-3/4	24391	100	21
18.0	P-181QT	Single gang, angled mid-nails, Quick Thread™ device holes	2-5/8	2-5/16	3-3/4	24399	100	21
18.0	P-181RK	Single gang, reverse nails, molded-in Speed Klamps™	2-11/16	2-5/16	3-3/4	24398	100	21
20.5	P-201	Single gang, angled nails	3-1/16	2-5/16	3-3/4	24900	100	23
20.5	P-201QT	Single gang, angled nails, Quick Thread™ device holes	3-1/8	2-5/16	3-3/4	24909	100	25
20.5	P-201R	Single gang, reverse nails	3-1/16	2-5/16	3-3/4	24901	100	24
23.5	P-122SC	Patented single gang with side cube, angled mid-nails, four wire knockouts, 2 recessed buttons	1-3/4	2-9/32 (5-1/2 overall)	3-3/4	24914	24	9
24.0	P-241	Single gang, angled nails	3-9/16	2-5/16	3-3/4	24903	100	26
24.0	P-241QT	Single gang, angled nails, Quick Thread™ device holes	3-9/16	2-5/16	3-3/4	24904	100	27



Face Bracket Mount

Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
			D	W	H			
18.0	P-181H	Single gang, face bracket mount, 1/2" NM knockouts	2-3/4	2-5/16	3-3/4	24916	48	10
18.0	P-181HZ	Single gang, face bracket mount, 1/2" NM knockouts, "Z" hanger	2-3/4	2-5/16	3-3/4	24919	36	11
24.0	P-241H	Single gang, face bracket mount	3-9/16	2-5/16	3-3/4	24907	50	12
24.0	P-241HQT	Single gang, face bracket mount, Quick Thread™ device holes	3-9/16	2-5/16	3-3/4	24908	50	12

Miscellaneous

Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
			D	W	H			
8.0	P-108E	Single gang, ears	1-1/4	2-5/16	3-3/4	24917	24	3
8.0	P-108H	Single gang, side bracket mount	1-1/4	2-5/16	3-3/4	24918	24	3
16.0	P-1160W	Single gang, ears, wing brackets, 1/2" NM knockouts	2-5/8	2-5/16	3-11/16	24915	48	10
18.0	P-1180W	Single gang, ears, wing brackets, molded-in Speed Klamps™, 1/2" NM knockout	3	2-1/4	3-11/16	92714	48	11
22.5	P-1220W	Single gang, ears, wing brackets, molded-in Speed Klamps™, 1/2" NM knockout	3-3/4	2-5/16	3-3/4	24913	48	14

All dimensions are in inches unless otherwise noted.
See page 32 for flexbox® Attachment Coding suffix descriptions.

Old Work/Manufactured Housing Boxes

Flush-Device Box
UL File No. E30594

Competitive Cross Reference

Fiberglass Outlet Boxes, Adjustable Boxes



ALLIED
MOULDED
PRODUCTS, Inc.

Vapor Seal fiberglassBOX™: Air-Sealed Fiberglass Boxes

Allied Moulded Vapor Seal	Carlton® PC	AIRFOIL, INC	Arlington Industries, Inc.	Nutek® (Airtight)	Hubbell (TradeSelect)
1099-NV	FN-23	SG-1	F101F / FN101F	F-WSW	2011FBA
1099-NV2	N/A	N/A	FN101FD	N/A	N/A
2302-HNKV2	N/A	N/A	FN102FD	N/A	N/A
2302-NKV	FN-236-V/NG-236-V	SG-2	F102F / FN102F	2-FWSW	2002FBA
3303-NKV	FN-354-V/NG-354-V	N/A	F103F / FN103F	3-FWSW	2003FBA
4304-NKV	FN-460-V/NG-460-V	N/A	F104F / FN104F	N/A	N/A
5305-NKV	N/A	N/A	N/A	N/A	N/A
5305-NBKV	N/A	N/A	N/A	N/A	N/A
9335-BHKV2	N/A	N/A	N/A	N/A	N/A
9335-HNKV2	N/A	N/A	N/A	N/A	N/A
9350-16KV	N/A	N/A	N/A	N/A	N/A
9350-BHKV	N/A	N/A	N/A	N/A	N/A
9350-BHKV2	N/A	N/A	N/A	N/A	N/A
9350-HNKV2	N/A	RD-1	FN440F	F-WOCT	2008FBA
9350-FRBKBV	N/A	N/A	FBR415F	N/A	N/A
9350-FRBKBV2	N/A	N/A	FBR425F	N/A	N/A
9351-NKV	FN-426-C-V	N/A	FN430F	N/A	N/A
9351-NKFRV	FN-CFB	FR-1	FB426F	N/A	N/A
9371-FRV	CFB-16-F	N/A	FB442F	N/A	7120VB
RD-42V	N/A	N/A	N/A	F-WRD	N/A

SLIDERBOX®: Adjustable Boxes

Allied Moulded SLIDERBOX®	Arlington Industries Inc. ONE-BOX™ & IN/OUT™ BOX	Carlton® PVC Adjust-A-Box™	Carlton® Steel Adjust-A-Box™	Smart Box Inc. Smart Box
SB-1	F101 / FA101 / FAS423	B121ADJ	MB120ADJ	MSB22+
SB-1H	F101H	B121ADJH	N/A	MSBHZ
SB-2	F102 / FA102	B234ADJ / B234ADJC	MB238ADJ	MSB2G
SB-3	F103 / FA103	B349ADJ	N/A	MSB3G
SB4	F104 / FA104	N/A	N/A	MSB4G
SB-CB	N/A	N/A	N/A	MSBRND
SB-CBG	N/A	N/A	N/A	N/A
SB-CBFR	FBS1423	N/A	N/A	MSBFAN