Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

1755 Enterprise Street
75751-0000, TX Athens
Phone: 903-675-7999
Fax: 903-675-9414



P2275 1800W Turnlok Photo Cell

Precision Multi Controls

Catalog Number	P2275
Manufacturer	Precision Multi Controls
Description	Photo Cell, 2.15 In Height, Polypropylene Housing Material, +158 °F Maximum Operating Temperature, -40 °F Minimum Operating Temperature, Built-In Time Delay Prevents False Cycling Caused By Lightning Flashes or Stray Headlights;Utility Grade Photocontrols Special Features, Culus Certified Standards Met, Contact Position At Night Normally Closed;Single-Pole;Single-Throw Switch Type, 120 V Voltage Rating, 1 Yr Warranty, 1800 W Wattage, 2 LB/Ea Weight
Weight per unit	2.0 (lbs/each)
Product Category	Lighting Photocells

Descriptions

Description	1800W TURNLOK PHOTO CELL

Manufacturer Information

Brand	Precision Multi Controls

Taxonomies, Classifications, and Categories

Category Description	Commercial dimmers, motion sensors, & photo cells

Packaging

Carton	1
Weight Per each	2