

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3450-104

Replay

Three-light inverted pendant from the Replay Collection, smooth forms, linear details and a pleasingly elegant frame enhance a simplified modern look.

Category: Pendants

Finish: Polished Nickel (plated)

Construction: Steel construction

Glass: Etched Outside, Painted White Inside glass bowl



Diameter: 16-5/8"
Height: 18-7/8"
Overall ht. w/chain: 92-1/2"

Glass: 14-3/8" dia.
Height: 4-1/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted Mounting strap for outlet box included Six feet 9 gauge chain supplied Canopy covers a standard 4" hexagonal recessed outlet box 5" dia., 7/8" depth	Pre-wired 15 feet of wire supplied 120V	Quantity: 3 100W Medium Base Medium porcelain sockets	UL-CUL Dry location listed 1 year warranty Companion Bath and Vanity, Chandelier, Close-to-ceiling, Hall and Foyer, Pendant, Wall bracket, fixtures are available