

Specifications



Photo is representative



Eaton P48G11S03P

Eaton Mini-Power Center, Single-phase, PV: 480V, Taps: 2 at -5% FCBN, SV: 120/240V, 115°C, 3 kVA, Al windings , Frame: 283, Indoor-Outdoor.

General specifications

PRODUCT NAME	Eaton Mini-Power center
CATALOG NUMBER	P48G11S03P
UPC	786680140136
PRODUCT LENGTH/DEPTH	8.9 in
PRODUCT HEIGHT	27.5 in
PRODUCT WIDTH	11.9 in
PRODUCT WEIGHT	130 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	NEMA Compliant
CERTIFICATIONS	UL Listed ANSI CSA Certified IEEE Certified



Powering Business Worldwide

Physical Attributes

COIL MATERIAL	Aluminum
ENCLOSURE	NEMA 3R
FRAME	283
TAP SIZE	2 at -5% FCBN
TYPE	Mini-power center
WIRING CONNECTION	97A3K

Miscellaneous

WEATHERSHIELD	Indoor-Outdoor
---------------	----------------

Performance Ratings

FREQUENCY RATING	60 Hz
PHASE	Single-phase
PRIMARY VOLTAGE	480 V
SECONDARY VOLTAGE	120/240 V
TEMPERATURE RISE	115 °C rise
VOLT AMPERE RATING	3 kVA

Resources

CATALOGS	Commercial Distribution, Transformers, Volume 2, Tab 2
MULTIMEDIA	Eaton's Transformer Flex Center
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - P48G11S03P

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton P48G11S03P

Eaton Mini-Power Center, Single-phase, PV:
480V, Taps: 2 at -5% FCBN, SV: 120/240V,
115°C, 3 kVA, Al windings , Frame: 283,
Indoor-Outdoor.

General specifications

PRODUCT NAME	Eaton Mini-Power center
CATALOG NUMBER	P48G11S03P
UPC	786680140136
PRODUCT LENGTH/DEPTH	8.9 in
PRODUCT HEIGHT	27.5 in
PRODUCT WIDTH	11.9 in
PRODUCT WEIGHT	130 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	NEMA Compliant
CERTIFICATIONS	UL Listed ANSI CSA Certified IEEE Certified



Powering Business Worldwide

Physical Attributes

COIL MATERIAL	Aluminum
ENCLOSURE	NEMA 3R
FRAME	283
TAP SIZE	2 at -5% FCBN
TYPE	Mini-power center
WIRING CONNECTION	97A3K

Miscellaneous

WEATHERSHIELD	Indoor-Outdoor
---------------	----------------

Performance Ratings

FREQUENCY RATING	60 Hz
PHASE	Single-phase
PRIMARY VOLTAGE	480 V
SECONDARY VOLTAGE	120/240 V
TEMPERATURE RISE	115 °C rise
VOLT AMPERE RATING	3 kVA

Resources

CATALOGS	Commercial Distribution, Transformers, Volume 2, Tab 2
MULTIMEDIA	Eaton's Transformer Flex Center
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - P48G11S03P

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

