

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P5683-31

Welbourne

The Welbourne collection features hexagonal framework with vine inspired scrolls and clear beveled glass panels. Cast aluminum construction with durable powder coat finish. One-light wall lantern.

Category: Outdoor

Finish: Textured Black (painted)

Construction: Die-cast aluminum construction

Glass: Clear beveled glass panels



Width: 9-3/8"

Height: 16"

Depth: 11-1/4"

H/CTR: 3-1/2"

Glass: 3-3/4" Top, 2-5/16" Bottom

Height: 7-1/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included Back plate covers a standard 4" hexagonal recessed outlet box 4-1/2", 7"ht.	Pre-wired 6" of wire supplied 120V	Quantity: 1 100W Medium Base Medium ceramic socket	UL-CUL Wet location listed 1 year warranty Companion Chain hung lantern, Post top lantern, Wall lantern fixtures are available

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P5683-31

Welbourne

The Welbourne collection features hexagonal framework with vine inspired scrolls and clear beveled glass panels. Cast aluminum construction with durable powder coat finish. One-light wall lantern.

Category: Outdoor

Finish: Textured Black (painted)

Construction: Die-cast aluminum construction

Glass: Clear beveled glass panels



Width: 9-3/8"

Height: 16"

Depth: 11-1/4"

H/CTR: 3-1/2"

Glass: 3-3/4" Top, 2-5/16" Bottom

Height: 7-1/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included Back plate covers a standard 4" hexagonal recessed outlet box 4-1/2", 7"ht.	Pre-wired 6" of wire supplied 120V	Quantity: 1 100W Medium Base Medium ceramic socket	UL-CUL Wet location listed 1 year warranty Companion Chain hung lantern, Post top lantern, Wall lantern fixtures are available