

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P5745-31

Ceiling Mount

Two-light non-metallic ceiling light with one-piece white acrylic diffuser and scalloped detail.

Category: Outdoor

Finish: Black (painted)

Construction:

Glass: White acrylic diffuser



Diameter: 10-1/4"

Height: 5-1/2"

Glass: 8-3/4" SQ

Height: 4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted Mounting strap for outlet box included	Pre-wired 6" of wire supplied 120V	Quantity: 2 60W Medium Base Medium porcelain sockets	UL Damp location listed 1 year warranty Companion fixtures are available

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P5745-31

Ceiling Mount

Two-light non-metallic ceiling light with one-piece white acrylic diffuser and scalloped detail.

Category: Outdoor

Finish: Black (painted)

Construction:

Glass: White acrylic diffuser



Diameter: 10-1/4"

Height: 5-1/2"

Glass: 8-3/4" SQ

Height: 4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Ceiling mounted</p> <p>Mounting strap for outlet box included</p>	<p>Pre-wired</p> <p>6" of wire supplied</p> <p>120V</p>	<p>Quantity: 2</p> <p>60W Medium Base</p> <p>Medium porcelain sockets</p>	<p>UL Damp location listed</p> <p>1 year warranty</p> <p>Companion fixtures are available</p>