



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## P68FSCBRN BRN Floor Ser CVR

*Abb Installation Products, Inc*

|                  |  |
|------------------|--|
| Catalog Number   | P68FSCBRN  |
| Manufacturer     | Abb Installation Products, Inc   |
| Description      | Carpet Plate and Cover For Flush Service Floor Box, 6 Inch Diameter, 1 Inch NPS Plug, Brown, Polycarbonate |
| Weight per unit  | 0.3000 (lbs/each)  |
| Product Category | Floor Boxes & Accessories  |

### Features

|           |              |
|-----------|--------------|
| Knockouts | FALSE        |
| Material  | Non-Metallic |

### Descriptions

|                        |  |
|------------------------|--|
| Description            | BRN FLOOR SER CVR  |
| extra long description | ABB P 68 FSC BRN 68 FSC BRN NON-MET  |
| Long Description       | Carpet Plate and Cover for Flush Service Floor Box, 6 Inch Diameter, 1 Inch NPS Plug, Brown, PolyCarbonate |
| Product Type           | 68 FSC BRN Non-Met. Service Cover  |

### Manufacturer Information

|                           |                           |
|---------------------------|---------------------------|
| Brand                     | Thomas&Betts-Abb Ins Prod |
| GTIN                      | 00785991619164            |
| Manufacturers Part Number | P 68 FSC BRN              |
| UPC                       | 785991619164              |

### Taxonomies, Classifications, and Categories

|                      |               |
|----------------------|---------------|
| Category Description | PLASTIC BOXES |
| Type                 | Flush Service |

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Weight Per each | 0.3 |

### Uses, Certifications, and Standards

|             |                             |
|-------------|-----------------------------|
| Application | For use with 68 P floor box |
| standard    | UL E11461 / UL E11461       |