



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



P814RQ Pan-Term® P8-14R-Q Ring T *Panduit Corporation*

| | |
|------------------|--|
| Catalog Number | P814RQ |
| Manufacturer | Panduit Corporation |
| Description | The P8-14R-Q Pan-Term® Terminal Is A Non-Insulated, Ring Terminal. Brazed Seam Protects Terminal Barrel From Splitting During The Crimp Process. Internal Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength. |
| Weight per unit | 0.2000 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|----------------|----------|
| connection | Standard |
| insulation | None |
| Material | Copper |
| media | Yes |
| Voltage Rating | 2000 |
| Wire Size | 8 |

Material, Color, and Finish

| | |
|--------|--------|
| Finish | Tinned |
|--------|--------|

Dimensions and Weight

| | |
|------|------|
| Size | 1/4" |
|------|------|

Descriptions

| | |
|------------------------|--|
| Description | PAN-TERM® P8-14R-Q RING T |
| extra long description | PAN P8-14R-Q Pan-Term® P8-14R-Q Rin |
| Long Description | The P8-14R-Q Pan-Term® Terminal is a non-insulated, ring terminal. Brazed seam protects terminal barrel from splitting during the crimp process. Internal barrel serrations assure good wire contact and maximum tensile strength. |
| Product Type | Pan-Term® P8-14R-Q Ring Terminal, Bare, 8 Awg, 1/4" Stud, PK |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Panduit® |
| GTIN | 00074983870790 |
| Manufacturers Part Number | P8-14R-Q |
| UPC | 074983870790 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------|
| Category Description | TERMINALS |
| Type | Ring Terminal |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-----|
| Carton | 25 |
| Package | 250 |
| Weight Per each | 0.2 |

Uses, Certifications, and Standards

| | |
|--------------------|---|
| Enclosure | Ring shape |
| Mounting | 3/8 |
| standard | cULus Listed 587H E52164, CSA Certified LR31212 |
| Temperature Rating | 302 Degrees Fahrenheit (150 Degrees Celsius) |