



# PENETROX Bottle 8 Ounce

By Burndy  
Catalog # P8A

Penetrox Bottle ,5.80 in Length ,2.04 in Width.



## Application

Aluminum to Aluminum, Aluminum to Conduit, Aluminum to Copper

## General

Application - For Use On	Aluminum to Aluminum; Aluminum to Conduit; Aluminum to Copper
Container Type	Squeeze Bottle
EU RoHS Indicator	Yes
Pour Point	-15 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	230 °F
Trade Name	PENETROX™
Type	Sealing compound
UPC	781810592557
UPC 12 Digit	7818105925577
Viscosity at 100 Fahrenheit	305 °F

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Container Size	8 oz
Minimum Pack Quantity	1

## Product Assets

- [3D Models - P8A\\_MODEL-IGES](#)
- [3D Models - P8A\\_MODEL-STEP](#)
- [3D Models - P8A\\_MODEL-PDF](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Sales Drawings - SC087702-01](#)
- [SDS - PENETROX\\_A\\_FRENCH\\_GHS](#)
- [SDS - PENETROX\\_A\\_GHS](#)
- [SDS - PENETROX\\_A\\_ESTONIAN\\_GHS](#)
- [SDS - PENETROX\\_A\\_PORTUGUESE\\_GHS](#)
- [SDS - PENETROX\\_A\\_ESPANOL\\_GHS](#)
- [SDS - PENETROX\\_A\\_GERMAN\\_GHS](#)



A proud member of the Hubbell Family.