

Product Number: 74250

Order Abbreviation: PANELF1A/040UNVD840/24G/WH

General Description: Edge Lit Panel 1A, 40 Watts, 120-277V, 0-10V Dimmable, 80+ CRI, 4000K, 2x4, white finish



Product Information

Power Factor	?0.90
Primary Lamp Type	SMD
Minimum Operating Temperature - Celsius	-20
Minimum Operating Temp - Fahrenheit	-4
Total Harmonic Distortion (THD)	?20 %
Efficacy (LPW)	110
Abbrev. With Packaging Info.	PANELF1A040UNVD84024GWH 3/CS 1/SKU
Color Temperature/CCT (K)	4000
Ordering Abbreviation	PANELF1A/040UNVD840/24G/WH
Average Rated Life 1 (hr)	50000
Lumens	4200
Nominal Voltage (V)	120.00
Nominal Wattage (W)	40.00
UPC Code	UPC046135742507
Color Rendering Index (CRI)	>80
Service Life Rating	?50000
Lumens (lm)	4200
Wattage (W)	40.00
Color Range	4000 K
Connectors	Terminal block
Energy Star Rated	No
Fixture Warranty	5 years
Housing	Aluminum
Luminaire Finish	White
Luminaire Type	Panel
Maximum Operating Temperature-Celsius	40
Maximum Operating Temperature-Fahrenheit	104
Power Input	40
Mounting	Recessed
Dimensions	47.8x23.82x1.71
Certification Listing	cETLus, FCC, RoHS, DLC