

Specifications



Photo is representative

Eaton PB2M-4XS

Eaton B-Line series push button enclosures, 5.75" height, 3" length, 3.25" width, NEMA 4X, Screw cover, PBM4XS enclosure, Surface mounted, Small single door, External mounting feet, 304 stainless steel, Oil-resistant gasket

General specifications

PRODUCT NAME	Eaton B-Line series push button enclosures
CATALOG NUMBER	PB2M-4XS
UPC	782051138146
PRODUCT LENGTH/DEPTH	3 in
PRODUCT HEIGHT	5.75 in
PRODUCT WIDTH	3.25 in
PRODUCT WEIGHT	2.1 lb
COMPLIANCES	Not Applicable
CERTIFICATIONS	Not Applicable



Material/finish

MATERIAL	304 stainless steel
----------	---------------------

Model

STYLE	Small single door
-------	-------------------

WALL THICKNESS	16 gauge
FINISH COLOR	#4 brushed
COLOR	Gray

MODEL	PBM4XS enclosure
COVER TYPE	Screw
MOUNTING METHOD	Surface
MOUNTING HOLE DETAILS	External mounting feet
SPECIAL FEATURES	Removable cover, recessed pull ring, s.s. screws

Standards	
NEMA RATING	4X
COUNTRY OF ORIGIN	US

Resources	
CATALOGS	Pushbutton-enclosure-operator.pdf
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - PB2M-4XS

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative

Eaton PB2M-4XS

Eaton B-Line series push button enclosures, 5.75" height, 3" length, 3.25" width, NEMA 4X, Screw cover, PBM4XS enclosure, Surface mounted, Small single door, External mounting feet, 304 stainless steel, Oil-resistant gasket

General specifications

PRODUCT NAME	Eaton B-Line series push button enclosures
CATALOG NUMBER	PB2M-4XS
UPC	782051138146
PRODUCT LENGTH/DEPTH	3 in
PRODUCT HEIGHT	5.75 in
PRODUCT WIDTH	3.25 in
PRODUCT WEIGHT	2.1 lb
COMPLIANCES	Not Applicable
CERTIFICATIONS	Not Applicable



Material/finish

MATERIAL	304 stainless steel
----------	---------------------

Model

STYLE	Small single door
-------	-------------------

WALL THICKNESS	16 gauge
FINISH COLOR	#4 brushed
COLOR	Gray

MODEL	PBM4XS enclosure
COVER TYPE	Screw
MOUNTING METHOD	Surface
MOUNTING HOLE DETAILS	External mounting feet
SPECIAL FEATURES	Removable cover, recessed pull ring, s.s. screws

Standards	
NEMA RATING	4X
COUNTRY OF ORIGIN	US

Resources	
CATALOGS	Pushbutton-enclosure-operator.pdf
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - PB2M-4XS

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

