

Specifications

Photo is representative



Eaton PDG23M0040TFFL

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Three Pole, 40A, 65kA/480V, T-M (Fxd-Fxd) TU, Standard Terminals Load Only (PDG2X3T100)

General specifications

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG23M0040TFFL
UPC	786679862049
PRODUCT LENGTH/DEPTH	88.9 mm
PRODUCT HEIGHT	152.4 mm
PRODUCT WIDTH	104.6 mm
PRODUCT WEIGHT	1.81890541 kg
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL 489 CCC Marked CSA IEC 60947-2

Delivery program

AMPERAGE RATING	40 A
CIRCUIT BREAKER FRAME TYPE	Complete breaker
FRAME	2
NUMBER OF POLES	Three-pole

Technical data - Electrical

VOLTAGE RATING	600 Vac
-----------------------	---------

General information

CIRCUIT BREAKER TYPE	PD2 Global
CLASS	Class A
TRIP TYPE	T298

Technical data - Mechanical - Terminals

TERMINALS	Standard Terminals Load Only
------------------	------------------------------

Technical information

INTERRUPT RATING 65 kAIC at 480 Vac

22 kAIC Icu @250 Vdc
100 kAIC @240V (UL)
50 kAIC Icu/ 30 kAIC Ics/ 105
kAIC Icm @480V Brazil (IEC)

INTERRUPT RATING RANGE

65 kAIC @480V (UL)
70 kAIC Icu/ 53 kAIC Ics/ 154
kAIC Icm @380-415V (IEC)
35 kAIC @600V (UL/CSA)
100 kAIC Icu/ 100 kAIC Ics/
220 kAIC Icm @240V (IEC)
30/25 kAIC Icu/ 15/13 kAIC
Ics @525V South Africa (IEC)
50 kAIC Icu/ 40 kAIC Ics/ 105
kAIC Icm @440V (IEC)
10 kAIC Icu/ 5 kAIC Ics/ 21
kAIC Icm @690V (IEC)
22 kAIC Icu @125 Vdc

Resources

3D CAD DRAWING PACKAGE

[Eaton Power Defense PDG23M0040TFFL 3D drawing](#)

APPLICATION NOTES

[Consulting application guide - molded case circuit breakers](#)

[Power Defense molded case circuit breaker selection poster](#)

[Power Defense brochure](#)

BROCHURES

[Power Defense technical selling booklet](#)

[Power Defense molded case circuit breakers - Frame 2 product aid](#)

CATALOGS

[Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2](#)

[PDG2 CB report](#)

[Power Defense Declaration concerning California's Proposition 65](#)

CERTIFICATION REPORTS

[PDG4 CCC certification](#)

[EU Declaration of Conformity - Power Defense molded case circuit breakers](#)

[PDG4 CB report](#)

INSTALLATION INSTRUCTIONS

[Power Defense Frame 2 PDG2 and PDC\(E\)9 breaker instructions - IL012106EN](#)

[Power Defense Frame 2 multi wire connector kit - PDG2X3\(2\)\(4\)TA2253W instructions - IL012243EN H01](#)

[Power Defense Frame 2 handle mech variable depth rotary handle instructions - IL012136EN](#)

[Power Defense Frame 2 Direct Rotary Handle Assy With Interlock Version Instructions \(IL012138EN\).pdf](#)

[Power Defense Frame 2 terminal kit - PDG2X3\(2\)\(4\)TA225RF instructions - IL012245EN H01](#)

[Power Defense Frame 2 screw terminal end cap kit, 225A, 3 pole instructions - IL012258EN H01](#)

[Power Defense Frame 1-2-3-4 IP door barrier assembly instructions - IL012278EN](#)

[Power Defense Frame 2 box terminal \(aluminum\), 225A, 3 pole instructions - IL012235EN H03](#)

[Power Defense Frame 1 IEC and Frame 2 Rotary Mechanism with NFPA Handle Attachment Instructions \(IL012260EN\).pdf](#)

[Power Defense Frame 2 multi wire connector kit - PDG2X3\(2\)\(4\)TA2256W instructions - IL012242EN H01](#)

[Power Defense Frame 2 shunt trip UVR instructions - IL012130EN](#)

[Power Defense Frame 2 tunnel terminal \(aluminum\), 50A, 3 pole instructions - IL012236EN H03](#)

[Power Defense Frame 2 tunnel terminal kits - PDG2X1TA225K instructions- IL012239EN H01](#)

[Power Defense Frame 2 global terminal shield, 3 pole - IL012330EN](#)

[Power Defense Frame 2 tunnel terminal \(aluminum\), 150A, 3 pole instructions - IL012238EN H03](#)

[Power Defense Frame 2 locking devices and handle block instructions - IL012149EN](#)

[Power Defense Frame 2 clamp terminal \(steel\), 20A, 3 pole instructions - IL012246EN H03](#)

[Power Defense Frame 2/3/4/5/6 voltage neutral sensor module wiring instructions – IL012316EN](#)

[Power Defense Frame 2 terminal kit - PDG2X3\(2\)\(4\)TA150RF instructions - IL012244EN H01](#)

[Power Defense Frame 2 tunnel terminal \(aluminum\), 100A, 3 pole instructions - IL012237EN H03](#)

[Power Defense Frame 2 motor circuit protector \(HMCP\) - IL012326EN](#)

[Power Defense Frame 2 box terminal \(steel\), 100A, 3 pole instructions - IL012234EN H03](#)

	Power Defense Frame 2 handle mech direct rotary handle instructions - IL012134EN
	Power Defense Frame 2 withTMTU, Shunt Trip, UVR Animated Instructions.rh
	Power Defense Frame 2 Handle Mech Variable Depth Rotary Handle Animated Instructions.rh
INSTALLATION VIDEOS	Power Defense Frame 2 Bell Alarm with PXR Animated Instructions.pdf.rh
	Power Defense Frame 2 Locking Devices and Handle Block Animated Instructions.pdf.rh
	Power Defense Frame 2 TMTU Aux, Alarm, ST and UVR Animated Instructions.rh
	Power Defense Frame 3 Variable Depth Rotary Handle Mechanism Installation How-To Video
	Power Defense Frame 2 Variable Depth Rotary Handle Mechanism Installation How-To Video
	Power Defense Frame 2 Direct Rotary Handle Mechanism Installation How-To Video
MULTIMEDIA	Power Defense Frame 2 Aux, Alarm, Shunt Trip, and UVR How-To Video
	Power Defense molded case circuit breakers
	Eaton Power Defense for superior arc flash safety
	Power Defense Breakers
	Power Defense Frame 5 Trip Unit How-To Video
	Power Defense Frame 6 Trip Unit How-To Video
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - PDG23M0040TFFL
TIME/CURRENT CURVES	Power Defense time current curves MCP Motor Circuit Protection – PD1, PD2, PD3
	Power Defense time current curve Frame 2 - PD2
WHITE PAPERS	Molded case and low-voltage power circuit breaker health
	Single and double break MCCB performance revisited

[Making a better machine](#)

[Intelligent circuit protection yields space savings](#)

[Molded case and low-voltage breaker health](#)

[Safer by design: arc energy reduction techniques](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

