



## PENA4

by Burndy  
Catalog ID: PENA4

Oxide Inhibiting Electrical Joint Compound, 4 OZ, For Al-Al, Al-Cu & Al Conduit Threads.

consists of a natural (petroleum) base vehicle in which zinc particles are suspended, UL Listed to 600 volts

## Product Details

### General

Application	Aluminum to Aluminum, Aluminum to Conduit, Aluminum to Copper
Application - For Use On	Aluminum to Aluminum; Aluminum to Conduit; Aluminum to Copper
Container Type	Squeeze Bottle
Pour Point	-15 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	230 °F
Trade Name	PENETROX™
Type	Sealing compound
UPC	781810593103
UPC 12 Digit	7818105931033
Viscosity at 100 Fahrenheit	305 °F

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Container Size	4 oz
Minimum Pack Quantity	1

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)