



Cover, Polymer Concrete, Tier 15, 13"x24"

By QUAZITE
Catalog # [PG1324HA0017](#)



*Representative Image

Features

- Stronger and lighter weight than regular concrete
- Cost effective
- Durable and long lasting
- Fire and chemical resistant
- Standard sizes are UL certified
- ANSI/SCTE77 certified
- Multiple styles and sizes available

General

EU RoHS Indicator	No
Insulated?	No
Load Rating (ANSI Tier)	T15
Logo Code	017
Logo Included?	Yes
Logo Text	Electric
Material	Polymer Concrete
UPC	662037109363
Weight Load Rating (Design/Test)	15,000/22,500 lb

Dimensions

Dimensions	24 in x 13 in x 2 in
Height	2 in
Length	24 in
Weight	51 lb
Width	13 in

Product Assets

- [Catalogs - Underground Enclosures \(CA07017E_UG_23_WEB\)](#)
- [Literature - Quazite® FRP Cover Options \(Logos\)](#)
- [Sales Drawings - Quazite 13 X 24 Cover Standard Version \(PG1324HA00\)](#)
- [Video - PenCell® How It's Made \(VI07068E0617\)](#)
- [Video - PenCell® Enclosures \(VI07062E0617\)](#)
- [Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
QUAZ-PG1324HA0017-SPEC-EN | REV 9/2023