



Cover, Polymer Concrete, Tier 15, 24"x36"

By QUAZITE
Catalog # [PG2436HA0017](#)



*Representative Image

Features

- Stronger and lighter weight than regular concrete
- Cost effective
- Durable and long lasting
- Fire and chemical resistant
- Standard sizes are UL certified
- ANSI/SCTE77 certified
- Multiple styles and sizes available

General

EU RoHS Indicator	No
Insulated?	No
Load Rating (ANSI Tier)	T15
Logo Code	017
Logo Included?	Yes
Logo Text	Electric
Material	Polymer Concrete
UPC	662037110826
Weight Load Rating (Design/Test)	15,000/22,500 lb

Dimensions

Dimensions	36 in x 24 in x 3 in
Height	3 in
Length	36 in
Weight	112 lb
Width	24 in

Product Assets

[Catalogs - Underground Enclosures \(CA07017E_UG_23_WEB\)](#)
[Literature - Quazite® FRP Cover Options \(Logos\)](#)
[Sales Drawings - Quazite Cover Standard Version \(PG2436HA00\)](#)
[Video - PenCell® How It's Made \(VI07068E0617\)](#)
[Video - PenCell® Enclosures \(VI07062E0617\)](#)
[Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
QUAZ-PG2436HA0017-SPEC-EN | REV 9/2023