ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
5004 National Parks highway
88220-0000, NM Carlsbad
Phone: 575-988-7017
Fax: 575-988-7018



PIWC4C 22-12AWG 4WR PSH-N Con

Nsi Industries

Catalog Number	PIWC4C
Manufacturer	Nsi Industries
Description	Push-In Connector, #22 Awg Conductor Size, #12 Awg Conductor Size, Insulated, Flame Retardant Polycarbonate Insulation Material, Copper;Tin Plated Stainle Conductor Material, Clear Insulation Color, 4 Conductors, -40 °F Operating Temperature, +221 °F Operating Temperature, 600 V, 0.81 LB/Ea
Weight per unit	0.8100 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Polycarbonate
Voltage Rating	600 V
Warranty	1 YEAR
Wire Type	COPPER

Material, Color, and Finish

Color	Clear
Finish	Polycarbonate

Dimensions and Weight

Depth	.748
Height	.411

Descriptions

Description	22-12AWG 4WR PSH-N CON
extra long description	NSI PIWC-4-C 22 - 12 Awg 4 Wire Pus
Features	Connecting wires is faster and easier than ever with the professional performance features of Easy-Twist wire connectors from NSI. Push-in connectors install quickly and form secure connections using a two-blade construction. Their clear bodies allow for visual inspection to save time and money. The expert team at NSI designed these connectors with key convenience and performance features for electrical industry professionals, including the integrated testing port for continuity testing and the compact, in

Manufacturer Information

GTIN	00662381159687
Manufacturers Part Number	PIWC-4-C
UPC	662381159687

Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

5004 National Parks highway
88220-0000, NM Carlsbad
Phone: 575-988-7017
Fax: 575-988-7018

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Push In Wire Connectors

Packaging

Carton	75
Weight Per each	0.81

Uses, Certifications, and Standards

Application	Splicing Wire
environmental conditions	105 C
standard	UL 486C