



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

12555 Harris Branch Pkwy Suite 105
78653-0000, TX Manor
Phone: 512-339-8750
Fax: 512-339-6732



PN148FC #14 Nyl FK Term *Panduit Corporation*

Catalog Number	PN148FC
Manufacturer	Panduit Corporation
Description	The PN14-8F-C Pan-Term® Terminal Is A Nylon Insulated, Fork Terminal. The Metal Insulation Grip Sleeve Crimps to Wire Insulation, Providing Protection and Strain Relief to The Crimp Joint For High Vibration Applications. Internal Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength.
Weight per unit	0.0006 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Standard
insulation	Nylon
Material	Copper
media	Yes
Voltage Rating	600
Wire Size	14

Material, Color, and Finish

Color	Blue
Finish	Tinned

Dimensions and Weight

Size	#8
------	----

Descriptions

Description	#14 NYL FK TERM
extra long description	PAN PN14-8F-C Pan-Term® PN14-8F-C F
Long Description	The PN14-8F-C Pan-Term® Terminal is a nylon insulated, fork terminal. The metal insulation grip sleeve crimps to wire insulation, providing protection and strain relief to the crimp joint for high vibration applications. Internal barrel serrations assure good wire contact and maximum tensile strength.
Product Type	Pan-Term® PN14-8F-C Fork Terminal, Blue, Nylon, 14-18 Awg, #

Manufacturer Information

Brand	PANDUIT
GTIN	00074983803101
Manufacturers Part Number	PN148FC
UPC	074983803101



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

12555 Harris Branch Pkwy Suite 105
78653-0000, TX Manor
Phone: 512-339-8750
Fax: 512-339-6732

Taxonomies, Classifications, and Categories

Category Description TERMINALS

Type Fork Terminal

Packaging

Carton 100

Weight Per each 0.0006

Uses, Certifications, and Standards

Enclosure Fork shape

Mounting 7/32

standard CSA Certified LR31212;UL Listed 587H E52164

Temperature Rating 221 Degrees Fahrenheit (105 Degrees Celsius)