



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PN1810FC #18 Nyl FK Term *Panduit Corporation*

Catalog Number	PN1810FC
Manufacturer	Panduit Corporation
Description	Fork Terminal, Nylon Insulated, 22- 18 Awg, #10 Stud Size, Standard Package.
Weight per unit	0.0006 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Standard
insulation	Nylon
Material	Copper
Voltage Rating	600
Wire Size	#18

Material, Color, and Finish

Color	Red
Finish	Tin-Plated

Dimensions and Weight

Size	#10
------	-----

Descriptions

Description	#18 NYL FK TERM
extra long description	PAN PN18-10F-C Pan-Term® PN18-10F-C
Long Description	Fork Terminal, nylon insulated, 22- 18 AWG, #10 stud size, standard package.
Product Type	Pan-Term® PN18-10F-C Loose Piece Forks

Manufacturer Information

Brand	PANDUIT
GTIN	00074983803040
Manufacturers Part Number	PN1810FC
UPC	074983803040

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Fork Terminal

Packaging

Carton	100
Weight Per each	0.0006



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Enclosure	Fork shape
Mounting	7/32
standard	UL Listed 587H E52164; CSA Certified LR31212
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)