Specifications



Photo is representative

Eaton PRL1A1600X42C

Eaton Pow-R-Stock PRL1A panelboard, Interior, 208Y/120V, Single-phase, 4W, 600A, Copper bus, 42 circuit

General specifications		
PRODUCT NAME	Eaton Pow-R-Stock PRL1A panelboard	
CATALOG NUMBER	PRL1A1600X42C	
UPC	786687010739	
PRODUCT LENGTH/DEPTH	67 in	
PRODUCT HEIGHT	7 in	
PRODUCT WIDTH	18 in	
PRODUCT WEIGHT	60 lb	
COMPLIANCES	NEMA Compliant	
CERTIFICATIONS	UL 67	



Product specifications

PRL1A Panelboard



AMPERAGE RATING	600A	
BUS MATERIAL	Copper	
BUS RATING	600 A	
FEED TYPE	Top/bottom	
NUMBER OF CIRCUITS	42	
NUMBER OF POLES	Single-pole, three-pole	
OPERATING TEMPERATURE	40°C	
PHASE	Single-phase	
RATED OPERATIONAL CURRENT	80%	
SHORT-CIRCUIT RATING	35 A	
VOLTAGE RATING	240V	
WIRE SIZE	#4 AWG-350 kcmil	
CIRCUIT BREAKER RATING	NEMA	
CURRENT - MAX	600 A	
INTERRUPT RATING	35 kAIC	
NEMA RATING	NEMA 1, NEMA 3R	
RATING OF FEEDERS	15-100	
SERIES	PRL1a	
TRIP RATING	600	
VOLTAGE - MAX	240 V	

MULTIMEDIA	Pow-R-Line Xpert family overview
SPECIFICATIONS AND	Eaton Specification Sheet -
DATASHEETS	PRL1A1600X42C

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

© 2025 Eaton. All Rights Reserved.

