



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS20AC1KL 20A 120/277VAC B+S Wire SP Key Lock SW

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | PS20AC1KL |
| Manufacturer | Pass & Seymour/Legrand |
| Description | 1POLE Key Lock Back and, Side Wire 20AMP 120/277volt |
| Weight per unit | 0.2237 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|-----------------|-----------------|
| action | SP |
| amperage rating | 20 |
| Contact Rating | 20Amp, 120/277V |
| insulation | False |
| Poles | 1 |
| Switch Type | Toggle |
| Voltage Rating | 120/277 |

Dimensions and Weight

| | |
|------|------|
| Size | 3.3" |
|------|------|

Descriptions

| | |
|------------------------|--|
| Description | 20A 120/277VAC B+S WIRE SP KEY LOCK SW |
| extra long description | P&S PS20AC1KL 20A 120/277VAC B+S WI |
| Long Description | 1pole Key Lock Back and, Side Wire 20amp 120/277volt |
| Product Type | 20A 120/277VAC B+S Wire SP Key Lock SW |
| Special Features | Heavy duty switch, back & side wire, shallow design for ease of installation with Key lock |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007195651 |
| Manufacturers Part Number | PS20AC1-KL |
| UPC | 785007195651 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | Commercial switches |
| Type | SWITCH |

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.2237 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Commercial/Residential |
| Mounting | WALL |
| standard | UL20 |