



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1121 W. 16th Street  
75455-0000, TX Mt. Pleasant  
Phone: 903-577-7311  
Fax: 903-577-7320



## PS20AC1LA 20A 120/277VAC B+S Wire SP SW La

*Pass & Seymour/Legrand*

Catalog Number	PS20AC1LA
Manufacturer	Pass & Seymour/Legrand
Description	1-Pole Toggle Switch, Back and Side-Wire, 20A 120/277V
Weight per unit	0.2142 (lbs/each)
Product Category	Gen Purpose Switches

### Features

action	SP
actuator	Toggle
amperage rating	20
Contact Rating	20 Amp, 120/277 VAC
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	CFL, Universal, Fluorescent, Incandescent, LED, Halogen, Xenon
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	1
Switch Type	Toggle
throw type	Single Throw
Voltage	120/277 V
Voltage Rating	120/277
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	3.3"
------	------

### Descriptions

Description	20A 120/277VAC B+S WIRE SP SW LA
extra long description	P&S PS20AC1LA 20A 120/277VAC B+S WI
Features	Chemical Resistant
Long Description	1-Pole Toggle Switch, Back and Side-Wire, 20A 120/277V
Product Type	20A 120/277VAC B+S Wire SP SW La
Special Features	Heavy duty switch, back & side wire, shallow design for ease of installation



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1121 W. 16th Street  
75455-0000, TX Mt. Pleasant  
Phone: 903-577-7311  
Fax: 903-577-7320

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007196641
Manufacturers Part Number	PS20AC1-LA
UPC	785007196641

## Taxonomies, Classifications, and Categories

Category Description	Miscellaneous residential devices
Type	SWITCH

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	50
Weight Per each	0.2142

## Uses, Certifications, and Standards

Application	Commercial/Residential
Mounting standard	WALL FEDSPEC, CULUS, UL20, FEDSPEC