



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1570 Lionel Drive  
79936-0000, TX El Paso  
Phone: 915-995-8443  
Fax: 915-245-2106



## PS20AC3L 20A 120/277VAC B+S Wire 3W Lock SW Gy

*Pass & Seymour/Legrand*

Catalog Number	PS20AC3L
Manufacturer	Pass & Seymour/Legrand
Description	3-Way Switch, 3 Poles, 3 Ways, 20 A, 120/277 V Ac, Nylon Material, Silver Cadmium Oxide Contact Material, Brown, Grounding Connection, Toggle Actuator, Wall Mount, 1.320 (L) X 1.073 (W) X 3.281 (H) In, -40 °C Operating Temperature, +115 °C Operating Temperature, 0.22 LB
Weight per unit	0.2240 (lbs/each)
Product Category	Gen Purpose Switches

### Features

action	TP
actuator	Toggle
amperage rating	20
Contact Rating	20 Amp, 120/277 VAC
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	Halogen, LED, CFL, Universal, Fluorescent, Incandescent, Xenon
Number of Gangs	1
Number of Switches	1.0
Poles	3-way
Switch Type	Toggle
throw type	Double Throw
Voltage	120 VAC, 277 VAC
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	3.3"
------	------

### Descriptions

Description	20A 120/277VAC B+S WIRE 3W LOCK SW GY
extra long description	P&S PS20AC3L 20A 120/277VAC B+S WIR

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007195637
Manufacturers Part Number	PS20AC3L
UPC	785007195637



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1570 Lionel Drive  
79936-0000, TX El Paso  
Phone: 915-995-8443  
Fax: 915-245-2106

## Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	SWITCH

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	50
Weight Per each	0.224

## Uses, Certifications, and Standards

Mounting	WALL
standard	CULUS, UL20, FEDSPEC