



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS30AC2I 30A 120/277VAC B+S Wire DP SW Iv

Pass & Seymour/Legrand

Catalog Number	PS30AC2I
Manufacturer	Pass & Seymour/Legrand
Description	Toggle Switch, 2 Poles, 30 A, 120/277 V Ac, Nylon Material, Silver Cadmium Oxide Contact Material, Ivory, Grounding Connection, Wall Mount, 1.437 (L) X 1.073 (W) X 3.281 (H) In, -40 °C Operating Temperature, +115 °C Operating Temperature, 0.23 LB
Weight per unit	0.2281 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	Double pole
amperage rating	30
Contact Rating	30Amp, 120/277Vac
insulation	False
Poles	2
Switch Type	Toggle
Voltage	120.0 V
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	30A 120/277VAC B+S WIRE DP SW I
extra long description	P&S PS30AC2I 30A 120/277VAC B+S WIR

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007195552
Manufacturers Part Number	PS30AC2I
UPC	785007195552

Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	TOGGLE SWITCH

Trade Size

Amperage	30.0
----------	------

Packaging

Carton	10
Package	50
Weight Per each	0.2281



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Enclosure	Nylon
Mounting	WALL
standard	CULUS, UL 498/20, FEDSPEC