

Hospital Grade -Extra-Hard Use (EHU) Plug, Black & Clear

PS5266XHG



Straight Blade Hospital Grade Plug, double pole and three wire, unit arrives completely ready-to-wire, cutting installation time significantly. Its nylon housing provides impact and chemical resistance. Its rugged two-piece cord grip provides more uniform cord retention andthe internal dust shield keeps terminals free of contaminants. 15amp 125volt.

features & benefits

- Tri-drive assembly screws are standard on Hospital Grade plugs and connectors (angle plugs not included).
- All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.
- Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.
- Cord-grip screws recessed to protect installer against screwdriver head slippage.



specifications

General Info

Color: Black

Listing Agencies/Third Party Information

CSA Listing Info: No CUL Listing No: No

cULus: Yes cURus: No Federal Spec: Yes UL Listing No: No UN SPS C: 39121402

UR: No

Dimensions

Depth U S: 1.752" Height U S: 1.516" Width U S: 1.516"

Technical Information

Volts A C: 125

Grade Type: Hospital

Buy American Act Compliance

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant