

Extra-Hard Use (EHU) Specification Grade Plug, Black & White

PS5366X



Straight Blade Plug 2pole 3wire 20amp
125v



features & benefits

- Unit arrives completely ready-to-wire, cuts installation time significantly.
- Nylon housing provides impact and chemical resistance.
- Rugged two-piece cord grip provides more uniform cord retention.
- Internal dust shield keeps terminals free of contaminants.
- Tri-drive assembly screws are standard on all Specification Grade plugs and connectors.
- All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.
- Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.
- Cord-grip screws recessed to protect installer against screwdriver head slippage.

specifications

General Info

Color: White, Black

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No.42

CSA Standard: Yes

Federal Spec: Yes

Fed Spec Number: WC596

UL Listing No: UL498
UL Standard: Yes
UN SPS C: 39121402

Dimensions

Depth U S: 1.752"
Height U S: 1.516"
Width U S: 1.516"

Technical Information

Volts A C: 125

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant