

Hospital Grade - Extra-Hard Use (EHU) Plug, Black & Clear

PS5366XHG



Straight Blade Plug 2pole 3wire 20amp
125volt Hospital Grade

features & benefits

- Unit arrives completely ready-to-wire, cuts installation time significantly.
- Nylon housing provides impact and chemical resistance.
- Rugged two-piece cord grip provides more uniform cord retention.
- Internal dust shield keeps terminals free of contaminants.
- Tri-drive assembly screws are standard on Hospital Grade plugs and connectors (angle plugs not included).
- All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.
- Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.
- Cord-grip screws recessed to protect installer against screwdriver head slippage.



specifications

General Info

Color: Black

Listing Agencies/Third Party Information

CSA Listing Info: No

CUL Listing No: No

cULus: Yes

cURus: No

Federal Spec: Yes
UL Listing No: No
UN SPS C: 39121402
UR: No

Dimensions

Depth U S: 1.752"
Height U S: 1.516"
Width U S: 1.516"

Technical Information

Volts A C: 125
Grade Type: Hospital

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant