



PLUGTAIL® HEAVY-DUTY COMPACT DESIGN HOSPITAL-GRADE DUPLEX RECEPTACLE, IVORY

PT8300HI | [Pass & Seymour](#)

FEATURES & BENEFITS

Factory-terminated devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each hospital-grade receptacle. The connector simply snaps into the back of the device—no fussing with wires, stripping or tightening screws. PlugTail devices are finger safe with no exposed terminals, so taping is not required. Now installation is a snap! PlugTail...The toughest and safest hospital-grade receptacles available.

For detailed PlugTail® information, visit our PlugTail Headquarters.



SPECIFICATIONS

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Auto-ground clip assures positive ground.

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Zinc-plated steel strap for added strength & ground connectivity.

Large brass contacts snugly terminate on device blade terminals. Audible snapping latch assures connection, allows release.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger-safe housing environment.

Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.

No exposed terminals before, during, or after installation increases safety at all phases of product life.

GENERAL INFO

Color: Ivory

Available Colors: Gray, Red, White, Black, Light Almond, Brown

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42
CSA Listed: Yes
CSA Standard: C22.2 No. 42
CUL Listing No: E140596
cUL Standard: Yes
Federal Spec: Yes
UL Listing No: E140596
UL Standard: UL498
UN SPSC: 3912406

DIMENSIONS

Depth (US): .625"
Height (US): 3.281"
Width (US): 1.5"

TECHNICAL INFORMATION

Amps: 20A
NEMA Configuration Number: 5-20R
NEMA Rating: Yes
Volts: 125V

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO





PLUGTAIL® HEAVY-DUTY COMPACT DESIGN HOSPITAL-GRADE DUPLEX RECEPTACLE, IVORY

PT8300HI | [Pass & Seymour](#)

FEATURES & BENEFITS

Factory-terminated devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each hospital-grade receptacle. The connector simply snaps into the back of the device—no fussing with wires, stripping or tightening screws. PlugTail devices are finger safe with no exposed terminals, so taping is not required. Now installation is a snap! PlugTail...The toughest and safest hospital-grade receptacles available.

For detailed PlugTail® information, visit our PlugTail Headquarters.



SPECIFICATIONS

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Auto-ground clip assures positive ground.

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Zinc-plated steel strap for added strength & ground connectivity.

Large brass contacts snugly terminate on device blade terminals. Audible snapping latch assures connection, allows release.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger-safe housing environment.

Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.

No exposed terminals before, during, or after installation increases safety at all phases of product life.

GENERAL INFO

Color: Ivory

Available Colors: Gray, Red, White, Black, Light Almond, Brown

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42
CSA Listed: Yes
CSA Standard: C22.2 No. 42
CUL Listing No: E140596
cUL Standard: Yes
Federal Spec: Yes
UL Listing No: E140596
UL Standard: UL498
UN SPSC: 3912406

DIMENSIONS

Depth (US): .625"
Height (US): 3.281"
Width (US): 1.5"

TECHNICAL INFORMATION

Amps: 20A
NEMA Configuration Number: 5-20R
NEMA Rating: Yes
Volts: 125V

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

