



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PTRA6STRB25 90 Degree 25" PT Conn Strand

Pass & Seymour/Legrand

Catalog Number	PTRA6STRB25
Manufacturer	Pass & Seymour/Legrand
Description	Connector, 2 Poles, Gray, 25 In Length, -40 °C Operating Temperature, +60 °C Operating Temperature
Weight per unit	0.0700 (lbs/each)
Product Category	Outlets, Jacks, & Plates

Features

Dielectric Strength	Withstands 2000V minimum
media	Yes
Number of Wires	3
Poles	Double Pole
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	12

Dimensions and Weight

Size	7.5
------	-----

Descriptions

Description	90 DEGREE 25" PT CONN STRAND
extra long description	P&S PTR A6STRB25 90 DEGREE 25 IN PT

Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007044577
UPC	785007044577

Taxonomies, Classifications, and Categories

Category Description	Residential cord connectors
Type	PlugTail™ Connector - Right Angle

Packaging

Carton	1
Package	25
Weight Per each	0.07

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	Device, Wall
standard	CULUS, cULus UL498