



PLUGTAIL® SWITCH RIGHT ANGLE CONNECTOR 4-WIRE, 6" STRANDED THHN12

PTS6STR4 | [Pass & Seymour](#)

FEATURES & BENEFITS

PlugTail® Switch Right Angle Connector, 4-wire, 6" Stranded THHN12, Colors Green, Red, Red, Black

For detailed PlugTail® information, visit our [PlugTail Headquarters](#).

- All PlugTail™ Connectors are available in any wire length up to 25 inches
- Large crimped and welded brass contacts
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing. Audible snapping latch assures connection, allows release.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Product Series: PlugTail
Type: Right Angle Connector
Number Of Poles: 3-way
Number Of Wires: 4
Style: Decorator

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

