



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PV1010LFL 12-10 Vnyl Ins LCKNG FRK Term Ylw # 10 Stud *Panduit Corporation*

Catalog Number	PV1010LFL
Manufacturer	Panduit Corporation
Description	The PV10-10LF-L Pan-Term® Terminal Is A Vinyl Insulated, Locking Fork Terminal. The Locking Tongue Design Locks In Place For A Secure Connection. Brazed Seam Protects Terminal Barrel From Splitting During The Crimp Process. Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength.
Weight per unit	0.2450 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Funnel
insulation	Vinyl
Material	Copper
media	Yes
Voltage Rating	600
Wire Size	10

Material, Color, and Finish

Color	Yellow
Finish	Tinned

Dimensions and Weight

Size	#10
------	-----

Descriptions

Description	12-10 VNYL INS LCKNG FRK TERM YLW # 10 STUD
extra long description	PAN PV10-10LF-L Pan-Term® PV10-10LF
Long Description	The PV10-10LF-L Pan-Term® Terminal is a vinyl insulated, locking fork terminal. The locking tongue design locks in place for a secure connection. Brazed seam protects terminal barrel from splitting during the crimp process. Barrel serrations assure good wire contact and maximum tensile strength.
Product Type	Pan-Term® PV10-10LF-L Fork Terminal, Yellow, Vinyl, 10-12 Aw

Manufacturer Information

Brand	PANDUIT
GTIN	00074983808168
Manufacturers Part Number	PV10-10LF-L
UPC	074983808168



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description TERMINALS

Type Locking Fork Terminal

Availability

minimum qty 50

Packaging

Carton 50

Package 500

Weight Per each 0.245

Uses, Certifications, and Standards

Enclosure Fork shape

Mounting 5/16

standard CSA Certified LR31212;UL Listed 587H E52164

Temperature Rating 221 Degrees Fahrenheit (105 Degrees Celsius)