



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PV148RC 16-14 Vinyl Ins Ring Terminal Blue # 8 Stud *Panduit Corporation*

Catalog Number	PV148RC
Manufacturer	Panduit Corporation
Description	The PV14-8R-C Pan-Term® Terminal Is A Vinyl Insulated, Ring Terminal. Brazed Seam Protects Terminal Barrel From Splitting During The Crimp Process. Internal Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength.
Weight per unit	0.3000 (lbs/each)
Product Category	Small Terminals & Connectors

### Features

connection	Funnel Entry
insulation	Vinyl
Material	Copper
media	Yes
Voltage Rating	600
Wire Size	#14

### Material, Color, and Finish

Color	Blue
Finish	Tinned

### Dimensions and Weight

Size	#8
------	----

### Descriptions

Description	16-14 VINYL INS RING TERMINAL BLUE # 8 STUD
extra long description	PAN PV14-8R-C Pan-Term® PV14-8R-C R
Long Description	The PV14-8R-C Pan-Term® Terminal is a vinyl insulated, ring terminal. Brazed seam protects terminal barrel from splitting during the crimp process. Internal barrel serrations assure good wire contact and maximum tensile strength.
Product Type	Pan-Term® PV14-8R-C Ring Terminal, Blue, Vinyl, 14-16 Awg, #

### Manufacturer Information

Brand	PANDUIT
GTIN	00074983801183
Manufacturers Part Number	PV14-8R-C
UPC	074983801183



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... TERMINALS

Type ..... Ring Terminal

## Availability

minimum qty ..... 100

## Packaging

Carton ..... 100

Package ..... 500

Weight Per each ..... 0.3

## Uses, Certifications, and Standards

Enclosure ..... Ring shape

Mounting ..... 5/16

standard ..... cULus Listed 587H E52164, CSA Certified LR31212

Temperature Rating ..... 221 Degrees Fahrenheit (105 Degrees Celsius)