



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PVC3X20 SCH 40 3" 20' PVC Conduit

Heritage Plastics

Catalog Number	PVC3X20
Manufacturer	Heritage Plastics
Description	PVC Conduit, Underground or Aboveground Application, Gray Color, 3.008 In Conduit Inner Diameter, 3.500 In Conduit Outer Diameter, 20 FT Length, Made In Usa, +90 °C Maximum Operating Temperature, 1760 FT/PK Package Quantity, Belled End;Corrosion Resistant:Rust Resistant:Sunlight Resistant;Rated For 90° Cable;Rigid Nonmetallic PVC Schedule 40 Special Features, Intertex Etl Listed Us;UI 651 and Nema TC2 Standards Met, 3 In Trade Size, 0.216 In Wall Thickness
Weight per unit	1.5 (lbs/each)
Product Category	PVC Conduit, Fittings, & Boxes

Descriptions

Description SCH 40 3" 20' PVC CONDUIT

Taxonomies, Classifications, and Categories

Category Description Conduit & Raceways - Pvc Conduit, Fittings, & Boxes

Availability

minimum qty 20

Packaging

Carton 20

Package 1760

Weight Per foot 1.45