

Specifications



Photo is representative

Eaton PVML-7-UNV1

Eaton Crouse-Hinds series Champ Pro PVML LED fixture, Cool white, 175W HID equivalent, No guard, Glass lens, 7000 lumens, 129 lm/W, Die cast aluminum, No mounting module, Type V, 100-277 Vac, 127-250 Vdc, 57W

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Champ Pro PVML LED light fixture
CATALOG NUMBER	PVML-7-UNV1
UPC	662276862050
PRODUCT LENGTH/DEPTH	13 in
PRODUCT HEIGHT	13.13 in
PRODUCT WIDTH	12.75 in
PRODUCT WEIGHT	20.8 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC IEC
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

LUMENS	7000
LUMENS PER WATT	129
COLOR TEMPERATURE	Cool white
MOUNTING METHOD	No mounting module
OPTICAL DISTRIBUTION	Type V
GUARD TYPE	No guard
VOLTAGE RATING	100-277 Vac, 127-250 Vdc
FREQUENCY RATING	50/60 Hz
WATTAGE	57W
DIMMING	Dimmable driver
POWER FACTOR	> 0.90
EQUIVALENT LUMINAIRE	175W HID
MATERIAL	Die cast aluminum
LENS MATERIAL	Heat and impact resistant glass

Resources

3D MODELS	SP3D Design Package - Champ Pro PVML Industrial LED Light Fixtures
BROCHURES	Crouse-Hinds series Global LED lighting portfolio Crouse-Hinds series DLC approved lighting products Crouse-Hinds series Champ Pro PVML LED Luminaires - 3,000 to 13,000 lumens brochure Crouse-Hinds series industrial LED lighting solutions
CATALOGS	Crouse-Hinds series Champ Pro PVML LED luminaires - 3,000 to 13,000 lumens catalog page
CERTIFICATION REPORTS	Champ Pro PVML Industrial LED Light Fixtures Canadian certification EC Declaration of Conformity - Crouse-Hinds series Champ Pro PVML LED Luminaires Champ Pro PVML Industrial LED Light Fixtures UL certification
INSTALLATION INSTRUCTIONS	IF 1888 - Champ VMVL and PVML Driver Replacement IF 1882 - Champ VMVL and PVML LED luminaires
SPECIFICATIONS AND DATASHEETS	Champ Pro PVM Industrial LED Eaton Specification Sheet - PVML-7-UNV1

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative

Eaton PVML-7-UNV1

Eaton Crouse-Hinds series Champ Pro PVML LED fixture, Cool white, 175W HID equivalent, No guard, Glass lens, 7000 lumens, 129 lm/W, Die cast aluminum, No mounting module, Type V, 100-277 Vac, 127-250 Vdc, 57W

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Champ Pro PVML LED light fixture
CATALOG NUMBER	PVML-7-UNV1
UPC	662276862050
PRODUCT LENGTH/DEPTH	13 in
PRODUCT HEIGHT	13.13 in
PRODUCT WIDTH	12.75 in
PRODUCT WEIGHT	20.8 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC IEC
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

LUMENS	7000
LUMENS PER WATT	129
COLOR TEMPERATURE	Cool white
MOUNTING METHOD	No mounting module
OPTICAL DISTRIBUTION	Type V
GUARD TYPE	No guard
VOLTAGE RATING	100-277 Vac, 127-250 Vdc
FREQUENCY RATING	50/60 Hz
WATTAGE	57W
DIMMING	Dimmable driver
POWER FACTOR	> 0.90
EQUIVALENT LUMINAIRE	175W HID
MATERIAL	Die cast aluminum
LENS MATERIAL	Heat and impact resistant glass

Resources

3D MODELS	SP3D Design Package - Champ Pro PVML Industrial LED Light Fixtures
BROCHURES	Crouse-Hinds series Global LED lighting portfolio Crouse-Hinds series DLC approved lighting products Crouse-Hinds series Champ Pro PVML LED Luminaires - 3,000 to 13,000 lumens brochure Crouse-Hinds series industrial LED lighting solutions
CATALOGS	Crouse-Hinds series Champ Pro PVML LED luminaires - 3,000 to 13,000 lumens catalog page
CERTIFICATION REPORTS	Champ Pro PVML Industrial LED Light Fixtures Canadian certification EC Declaration of Conformity - Crouse-Hinds series Champ Pro PVML LED Luminaires Champ Pro PVML Industrial LED Light Fixtures UL certification
INSTALLATION INSTRUCTIONS	IF 1888 - Champ VMVL and PVML Driver Replacement IF 1882 - Champ VMVL and PVML LED luminaires
SPECIFICATIONS AND DATASHEETS	Champ Pro PVM Industrial LED Eaton Specification Sheet - PVML-7-UNV1

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

