



GE  
Lighting

24929 - GE Q300T3CL/PRO-6PK

Q300T3CL/PRO-6PK

Product Photo



#### GENERAL CHARACTERISTICS

Rated Life Hours-nominal	2000 h
Primary Application	Standard <General Purpose>
Product Technology	Halogen
Bulb Shape	T2.5

#### PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	19
Initial Lumens-nominal	5760 lm
Color Temperature	2900 K

#### PRODUCT INFORMATION

Product Code	24929
Description	Q300T3CL/PRO-6PK
Alternative Unit Of Measure	EACH
Standard Package Quantity	144
Ean UPC	043168249294
Standard Package GTIN	00043168249294
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	144
Sales Unit	Each
UCC	043168249294
Alternative Unit Of Measure	CASE

#### ELECTRICAL CHARACTERISTICS

Input Voltage [nom]	120 V
Rated power (Watts)	300 W



GE  
Lighting

24929 - GE Q300T3CL/PRO-6PK

Q300T3CL/PRO-6PK

Product Photo



#### GENERAL CHARACTERISTICS

Rated Life Hours-nominal	2000 h
Primary Application	Standard <General Purpose>
Product Technology	Halogen
Bulb Shape	T2.5

#### PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	19
Initial Lumens-nominal	5760 lm
Color Temperature	2900 K

#### PRODUCT INFORMATION

Product Code	24929
Description	Q300T3CL/PRO-6PK
Alternative Unit Of Measure	EACH
Standard Package Quantity	144
Ean UPC	043168249294
Standard Package GTIN	00043168249294
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	144
Sales Unit	Each
UCC	043168249294
Alternative Unit Of Measure	CASE

#### ELECTRICAL CHARACTERISTICS

Input Voltage [nom]	120 V
Rated power (Watts)	300 W