



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

QA342N  
 7818103166033  
 400-500 2 HOLE NEMA  
 Active

**Web Use**  
 BURNDY Product Line

Dimensional	
Height (Fraction) (in)	2
Length (in)	4.69
Thickness (in)	22/71
Height (in)	1.94
D or Diameter (Fraction) (in)	3-3/32
Hole Size (Fraction)	9/16
Stud Size (in)	1/2
Thickness	0.31
D - in	3.09
Pad Width (in)	1.38
N (Fraction)	5/8
E - in	1.75
N (in)	0.62
Hole Size (in)	0.56
Length (Fraction)	4-11/16
General	
Number of Holes	2
Product Description	Copper Terminal, Heavy Duty, 2 Hole, 400-500 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, 1 Screw
Conductor(s)	
Copper Solid Size (Range)	N/A
Navy Cable Size (Range)	400 (127) Navy-500 (127) Navy
Copper Stranded (Range)	400 kcmil-500 kcmil
Physical	
Installation Torque	375
Type of Plating	Unplated
Connector Type	Terminal
Plated (Yes or No)	N
Product Material	Copper
Approvals / Certifications	
UL Listed	Y
CSA Certified	N
ROHS Compatible	Exempt
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B
Documentation	

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175