

# Specifications

## Eaton QB1030GF

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 30A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, Bolt-on, #14-4 AWG, QB



Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton QB GFCI circuit breaker
<b>CATALOG NUMBER</b>	QB1030GF
<b>UPC</b>	786680222429
<b>PRODUCT LENGTH/DEPTH</b>	4 in
<b>PRODUCT HEIGHT</b>	1 in
<b>PRODUCT WIDTH</b>	3.5 in
<b>PRODUCT WEIGHT</b>	0.45 lb
<b>WARRANTY</b>	1 year
<b>COMPLIANCES</b>	Contact Manufacturer
<b>CERTIFICATIONS</b>	UL 489

## Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QB
<b>CONNECTION</b>	Bolt-on
<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Single-pole
<b>TYPE</b>	Ground fault circuit breaker
<b>WIRE SIZE</b>	#14-4 AWG

## Performance Ratings

<b>AMPERAGE RATING</b>	30 A
<b>INTERRUPT RATING</b>	10 kAIC
<b>TRIP TYPE</b>	Non-Interchangeable
<b>TRIP RATING</b>	5 mA trip sensitivity
<b>VOLTAGE RATING</b>	120/240 V

## Resources

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - QB1030GF](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
All other trademarks are property of their respective owners.



# Specifications

## Eaton QB1030GF

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 30A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, Bolt-on, #14-4 AWG, QB



Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton QB GFCI circuit breaker
<b>CATALOG NUMBER</b>	QB1030GF
<b>UPC</b>	786680222429
<b>PRODUCT LENGTH/DEPTH</b>	4 in
<b>PRODUCT HEIGHT</b>	1 in
<b>PRODUCT WIDTH</b>	3.5 in
<b>PRODUCT WEIGHT</b>	0.45 lb
<b>WARRANTY</b>	1 year
<b>COMPLIANCES</b>	Contact Manufacturer
<b>CERTIFICATIONS</b>	UL 489

## Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QB
<b>CONNECTION</b>	Bolt-on
<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Single-pole
<b>TYPE</b>	Ground fault circuit breaker
<b>WIRE SIZE</b>	#14-4 AWG

## Performance Ratings

<b>AMPERAGE RATING</b>	30 A
<b>INTERRUPT RATING</b>	10 kAIC
<b>TRIP TYPE</b>	Non-Interchangeable
<b>TRIP RATING</b>	5 mA trip sensitivity
<b>VOLTAGE RATING</b>	120/240 V

## Resources

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - QB1030GF](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
All other trademarks are property of their respective owners.

