

Specifications

Eaton QBGFEP2015

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, Bolt-on mounting, 15A, 10 kAIC, Two-pole, 120/240V, Non-Interchangeable, 30 mA Trip sensitivity, QBGFEP

Physical Attributes

CIRCUIT BREAKER TYPE	QBGFEP
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker

General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFEP2015
UPC	786679473474
PRODUCT LENGTH/DEPTH	5 in
PRODUCT HEIGHT	3.5 in
PRODUCT WIDTH	2 in
PRODUCT WEIGHT	0.66 lb
WARRANTY	1 year
CERTIFICATIONS	UL 943
CATALOG NOTES	HACR rated



Specifications

Eaton QBGFEP2015

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, Bolt-on mounting, 15A, 10 kAIC, Two-pole, 120/240V, Non-Interchangeable, 30 mA Trip sensitivity, QBGFEP

Physical Attributes

CIRCUIT BREAKER TYPE	QBGFEP
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker

General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFEP2015
UPC	786679473474
PRODUCT LENGTH/DEPTH	5 in
PRODUCT HEIGHT	3.5 in
PRODUCT WIDTH	2 in
PRODUCT WEIGHT	0.66 lb
WARRANTY	1 year
CERTIFICATIONS	UL 943
CATALOG NOTES	HACR rated

