

Eaton QBGFEP2040

Catalog Number: QBGFEP2040

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, Bolt-on mounting, 40A, 10 kAIC, Two-pole, 120/240V, Non-Interchangeable, QBGF

General specifications



Product Name	Catalog Number
Eaton QB GFCI circuit breaker	QBGFEP2040
UPC	Product Length/Depth
786679145180	6.125 in
Product Height	Product Width
2.25 in	3.5 in
Product Weight	Certifications
0.85 lb	UL 943
Catalog Notes	
HACR rated	

Physical Attributes

Circuit breaker type

QBGF

Number of poles

Two-pole

Type

Ground fault circuit breaker

Performance Ratings

Amperage Rating

40 A

Interrupt rating

10 kAIC

Trip Type

Non-Interchangeable

Voltage rating

120/240 V

Miscellaneous

Special features

Bolt-on mounting

Resources

Specifications and datasheets

[Eaton Specification Sheet - QBGFEP2040](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)