

# Specifications

## Eaton QBGFEP2050

Eaton QB GFCI circuit breaker,Ground fault circuit breaker,Bolt-on mounting,50A,10 kAIC,Two-pole,120/240V,Non-Interchangeable,30 mA Trip sensitivity,QBGFEP

### General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFEP2050
UPC	786679145203
PRODUCT LENGTH/DEPTH	5.8 in
PRODUCT HEIGHT	4.4 in
PRODUCT WIDTH	3 in
PRODUCT WEIGHT	0.9 lb
WARRANTY	1 year
CERTIFICATIONS	UL 943
CATALOG NOTES	HACR rated

## Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QBGFEP
<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Two-pole
<b>TYPE</b>	Ground fault circuit breaker

## Miscellaneous

<b>SPECIAL FEATURES</b>	Bolt-on mounting
-------------------------	------------------

## Performance Ratings

<b>AMPERAGE RATING</b>	50 A
<b>INTERRUPT RATING</b>	10 kAIC
<b>TRIP TYPE</b>	Non-Interchangeable
<b>TRIP RATING</b>	30 mA trip sensitivity
<b>VOLTAGE RATING</b>	120/240 V

## Resources

### CATALOGS

[Circuit Protection, Miniature Circuit Breakers and Supplementary Protectors, Volume 4, Tab 1](#)

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - QBGFEP2050](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton QBGFEP2050

Eaton QB GFCI circuit breaker,Ground fault circuit breaker,Bolt-on mounting,50A,10 kAIC,Two-pole,120/240V,Non-Interchangeable,30 mA Trip sensitivity,QBGFEP

### General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFEP2050
UPC	786679145203
PRODUCT LENGTH/DEPTH	5.8 in
PRODUCT HEIGHT	4.4 in
PRODUCT WIDTH	3 in
PRODUCT WEIGHT	0.9 lb
WARRANTY	1 year
CERTIFICATIONS	UL 943
CATALOG NOTES	HACR rated

## Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QBGFEP
<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Two-pole
<b>TYPE</b>	Ground fault circuit breaker

## Miscellaneous

<b>SPECIAL FEATURES</b>	Bolt-on mounting
-------------------------	------------------

## Performance Ratings

<b>AMPERAGE RATING</b>	50 A
<b>INTERRUPT RATING</b>	10 kAIC
<b>TRIP TYPE</b>	Non-Interchangeable
<b>TRIP RATING</b>	30 mA trip sensitivity
<b>VOLTAGE RATING</b>	120/240 V

## Resources

### CATALOGS

[Circuit Protection, Miniature Circuit Breakers and Supplementary Protectors, Volume 4, Tab 1](#)

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - QBGFEP2050](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

