

# Eaton QBGFEP2050

Catalog Number: QBGFEP2050

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, Bolt-on mounting, 50A, 10 kAIC, Two-pole, 120/240V, Non-Interchangeable, 30 mA Trip sensitivity, QBGFEP

## General specifications



Product Name	Catalog Number
Eaton QB GFCI circuit breaker	QBGFEP2050
UPC	Product Length/Depth
786679145203	5.8 in
Product Height	Product Width
4.4 in	3 in
Product Weight	Warranty
0.9 lb	1 year
Certifications	Catalog Notes
UL 943	HACR rated

## Physical Attributes

**Circuit breaker type**  
QBGFEP

**Mounting Method**  
Bolt-on

**Number of poles**  
Two-pole

**Type**  
Ground fault circuit breaker

## Performance Ratings

**Amperage Rating**  
50 A

**Interrupt rating**  
10 kAIC

**Trip Type**  
Non-Interchangeable

**Trip rating**  
30 mA trip sensitivity

**Voltage rating**  
120/240 V

## Miscellaneous

**Special features**  
Bolt-on mounting

## Resources

**Brochures**  
[Loadcenters and Circuit Breakers](#)

**Catalogs**  
[Eaton's Volume 4—Circuit Protection](#)

**Specifications and datasheets**  
[Eaton Specification Sheet - QBGFEP2050](#)  
[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton QBGFEP2050

Catalog Number: QBGFEP2050

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, Bolt-on mounting, 50A, 10 kAIC, Two-pole, 120/240V, Non-Interchangeable, 30 mA Trip sensitivity, QBGFEP

## General specifications



Product Name	Catalog Number
Eaton QB GFCI circuit breaker	QBGFEP2050
UPC	Product Length/Depth
786679145203	5.8 in
Product Height	Product Width
4.4 in	3 in
Product Weight	Warranty
0.9 lb	1 year
Certifications	Catalog Notes
UL 943	HACR rated

## Physical Attributes

**Circuit breaker type**  
QBGFEP

**Mounting Method**  
Bolt-on

**Number of poles**  
Two-pole

**Type**  
Ground fault circuit breaker

## Performance Ratings

**Amperage Rating**  
50 A

**Interrupt rating**  
10 kAIC

**Trip Type**  
Non-Interchangeable

**Trip rating**  
30 mA trip sensitivity

**Voltage rating**  
120/240 V

## Miscellaneous

**Special features**  
Bolt-on mounting

## Resources

**Brochures**  
[Loadcenters and Circuit Breakers](#)

**Catalogs**  
[Eaton's Volume 4—Circuit Protection](#)

**Specifications and datasheets**  
[Eaton Specification Sheet - QBGFEP2050](#)  
[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)