

Eaton QBGFEP2050

Catalog Number: QBGFEP2050

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, Bolt-on mounting, 50A, 10 kAIC, Two-pole, 120/240V, Non-Interchangeable, 30 mA Trip sensitivity, QBGFEP

General specifications



| | |
|-------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton QB GFCI circuit breaker | QBGFEP2050 |
| UPC | Product Length/Depth |
| 786679145203 | 5.8 in |
| Product Height | Product Width |
| 4.4 in | 3 in |
| Product Weight | Warranty |
| 0.9 lb | 1 year |
| Certifications | Catalog Notes |
| UL 943 | HACR rated |

Physical Attributes

Circuit breaker type

QBGFEP

Mounting Method

Bolt-on

Number of poles

Two-pole

Type

Ground fault circuit breaker

Performance Ratings

Amperage Rating

50 A

Interrupt rating

10 kAIC

Trip Type

Non-Interchangeable

Trip rating

30 mA trip sensitivity

Voltage rating

120/240 V

Miscellaneous

Special features

Bolt-on mounting

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - QBGFEP2050](#)

[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)