

Specifications

Eaton QBGFT1015

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 15A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, #14–10 Cu, #12–10 Al, QBGF

Physical Attributes

CIRCUIT BREAKER TYPE	QBGF
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Single-pole
TYPE	Ground fault circuit breaker
WIRE SIZE	#14-10 AWG Cu #12-10 AWG Al

General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFT1015
UPC	786680130953
PRODUCT LENGTH/DEPTH	1 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	0.5 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489



Powering Business Worldwide