

# Specifications

## Eaton QBGFT1015



Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 15A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, #14-10 Cu, #12-10 Al, QBGF

### General specifications

<b>PRODUCT NAME</b>	Eaton QB GFCI circuit breaker
<b>CATALOG NUMBER</b>	QBGFT1015
<b>UPC</b>	786680130953
<b>PRODUCT LENGTH/DEPTH</b>	1 in
<b>PRODUCT HEIGHT</b>	1 in
<b>PRODUCT WIDTH</b>	1 in
<b>PRODUCT WEIGHT</b>	0.5 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL 489

Physical Attributes	
CIRCUIT BREAKER TYPE	QBGF
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Single-pole
TYPE	Ground fault circuit breaker
WIRE SIZE	#14-10 AWG Cu #12-10 AWG Al

Miscellaneous	
SPECIAL FEATURES	5 mA Trip Sensitivity

Performance Ratings	
AMPERAGE RATING	15 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Non-Interchangeable
TRIP RATING	5 mA trip sensitivity
VOLTAGE RATING	120/240 V

Resources	
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - QBGFT1015</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

