

Specifications

Photo is representative



Eaton QBGFT1040

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 40A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, #8 Cu, #8-6 Al, QBGF

Physical Attributes

| | |
|-----------------------------|------------------------------|
| CIRCUIT BREAKER TYPE | QBGF |
| MOUNTING METHOD | Bolt-on |
| NUMBER OF POLES | Single-pole |
| TYPE | Ground fault circuit breaker |
| WIRE SIZE | #8 Cu #8-6 Al |

General specifications

| | |
|-----------------------------|-------------------------------|
| PRODUCT NAME | Eaton QB GFCI circuit breaker |
| CATALOG NUMBER | QBGFT1040 |
| UPC | 786680130991 |
| PRODUCT LENGTH/DEPTH | 1 in |
| PRODUCT HEIGHT | 1 in |
| PRODUCT WIDTH | 1 in |
| PRODUCT WEIGHT | 0.5 lb |
| WARRANTY | 1 year |
| CERTIFICATIONS | UL 489 |

EATON

Powering Business Worldwide